

◆ Instructions for use:

Open the dryer box, take out the dryer, and check its shape, if there is no damage; go on with following steps:

1. Place or fix the dryer, connecting the hose with connection screw, fastening clockwise with 45 degree.
2. Plug in the dryer (please make sure the power supply voltage match the machine);
3. Switch on the dryer and adjust it to desired wind speed and temperature (air flow and temperature adjustable). Then the dryer can be engaged in work

Important Notice

1. This machine use AC power source, power must thus have a good grounding device
2. To maintain a smooth flow of air the air intakes can not be put close to water, preventing taking in water which may damage the machine.
3. Clean the filters regularly to ensure a smooth air flow.
4. If the motor does not work after plug in, please turn off heat switch immediately to avoid damage to heating element.
5. Do not let minors be close to or play with the machine!

Maintenance Instruction

1. The shell of the machine can be cleaned with a soft cloth and neutral detergent solution (to avoid spoiling the paint work) then use a dry cloth to clean it;
2. Use water or strong fan to clean the filters regularly. Note that filters can not be fixed on the machine until it is totally dry, in case the water may damage the machine. The machine has a standby filter with it.
3. When the machine runs out of carbon brush, professionals should be invited to check and update a new carbon brush.

Pets Water Blower Instruction for Use


Water Blower Model

LT-1090A



LT-1090A Structure Representation

NO	Name	Amount
1	Air outlet	3
2	Components for the heat-insulating cover	1
3	retractable hose	1
4	Front cover component	1
5	electric heating component	1
6	heat and radiation shield	1
7	motor stand	1
8	electric fan	1
9	anti-vibration pad for motors	1
10	case component	1
11	inner noise elimination cover	1
12	filter	1
13	trail cover	1
14	outer noise elimination cover	1
15	screw nuts for trail cover	1
16	power switch signal	1
17	power switch	
18	velocity adjustment knob	1
19	heating switch	1
20	heating signal	1



LT-1090A Structure Representation

Product Features and Parameters

1. Model: LT-1090A
2. Specification: Stepless speed, two gears temperature.
3. Voltage: AC 220V, 50HZ
4. Power: 500W-2400W
5. Wind speed: 25m/s-50m/s
6. Temperature: 30°C-70°C

Functions & Features

1. Soft Start:

Thanks to the protection from current buffers, when started, the dryers will not discharge any impulse current, exerting no adverse influence upon the neighboring working electrical equipments.

2. Low Noise and Powerful Airflow

The specially-designed noise reduction devices at air inlets are conducive to improving studios' environment, ensuring pet's serenity, easing the restlessness and offering convenience to nursing operators. With 10%-greater airflow than any other single-motor dryers, this model can dry your pets quickly and benefit pets' health.

3. Full Function:

This model is especially designed with high speed setting, which can work at full speed, as well as minimum airflow and high-heat settings, which have all the functions of handheld dryer.

4. Special Humanized Design

Plastic material for whole dryer shell makes the dryer more safely use after it turns on. Equipped with quick locking system for the hose connecting part, and this makes the dryer much convenient to install. Added handle on the hose to prevent from hot temperature after using long time.